

FLUKE TOOL UP FOR TAX TIME SALE

FLUKE®

OFFERS VALID TILL 30 JUNE 2020/ OR UNTIL STOCKS LAST.

DON'T WAIT FOR YOUR TAX RETURN TO BENEFIT. TAKE ADVANTAGE OF THE GOVERNMENT'S INSTANT TAX WRITE OFF.

Fluke Installation Multifunction Testers

The Fluke 1660 Series Installation Testers verify the safety of electrical installations in domestic, commercial and industrial applications. They are easy to use and ensure that fixed wiring is safe and correctly installed to meet local standards.

Specifications	1662 AU	1663/FVF AU	1664 FC/FVF AU
Insulation PreTest™ safety functions			●
Insulation at L-N, L-PE, N-PE inputs			●
Auto Test Sequence			●
Fluke Connect® compatibility			●
Test smooth DC sensitive RCD's (Type B/B+)		●	●
Earth resistance		●	●
Covering all basic installation test functions	●	●	●
Fluke FVF-SC2 reporting software included		●	●

Fluke 1662 Deal



Purchase
Fluke 1662/AU Multifunction
Installation Tester



Receive FREE
Fluke T5-600
Voltage, Continuity
and Current Tester

Valued at \$283.00

Fluke 1663 Deal



Purchase
Fluke 1663/FVF/AU
Multifunction Installation Tester
with FVF-SC2 FlukeView
Forms Software



Receive FREE
Fluke T6-1000
Electrical Tester

Valued at \$439.00

Fluke 1664 FC Deal



Purchase
Fluke 1664 FC/FVF/AU
Multifunction Installation Tester
with FVF-SC2 FlukeView
Forms Software



Receive FREE
Fluke T6-1000
Electrical Tester

Valued at \$439.00

Fluke Digital Multimeters

When Uptime Matters

Whether you work in the residential or commercial world, deal with HVAC equipment or electricity Fluke has a full family of digital multimeters for you.

Fluke 110 Series Digital Multimeter

Function/Features	114	115	116	117
True RMS Readings	AC	AC	AC	AC
Voltage AC/DC	600 V	600 V	600 V	600 V
Current AC/DC	-	10.0 A	600.0 μ A	10.0 A
Temperature	-	-	+400°C	-
Diode Test	-	Yes	Yes	Yes
LoZ	Yes	-	Yes	Yes
VoltAlert Non-Contact Volatage Detector	-	-	-	Yes
Safety Rating (EN 61010)	CAT III 600V	CAT III 600V	CAT III 600V	CAT III 600V

Fluke 110 Series Deal



Purchase
Fluke 114, 115,
116 or 117 Digital
Multimeter

Receive FREE
Fluke TPAK ToolPak™
Magnetic Meter Hanger
+ Fluke Ergonomic
Bottle Opener

Valued at \$108.00



Fluke 179 True-RMS Digital Multimeter

- True RMS voltage and current measurements
- 0.09% basic accuracy
- 6000 count resolution
- Temperature measurements

Fluke 179 Deal



Purchase
Fluke 179
True-RMS
Digital
Multimeter



Receive FREE
Fluke TLK225 Master
Accessory Set

Valued at \$282.00

NEW



Fluke 87V MAX True-RMS Digital Multimeter

- Waterproof, dustproof IP67 case withstands drops up to 4-metres
- Supports accurate measurements on VFDs using a low-pass filter
- Captures intermittents as fast as 250 μ s with Peak Capture

Fluke 87V MAX Deal



Purchase
Fluke 87V MAX
Industrial
Multimeter



Receive FREE
Fluke TLK289 Industrial
Master Test Lead Set

Valued at \$314.00



Fluke 789 ProcessMeter™

- Combines the functionality of a loop calibrator with the power of a precision 1000 V, 440 mA True-RMS digital multimeter
- Includes 24 V loop power supply

Fluke 789 Deal



Purchase
Fluke 789
ProcessMeter™



Receive FREE
Fluke i400 AC Current Clamp

Valued at \$331.00



Fluke 1587 FC Insulation Multimeter

- PI/DAR timed ratio tests
- Live circuit detection prevents insulation test if voltage > 30 V is detected for added user protection
- VFD low-pass filter for accurate motor drive measurements

Fluke 1587FC Deal



Purchase
Fluke 1587 FC
Insulation
Multimeters



Receive FREE
Fluke 325 True
RMS Clamp Meter

Valued at \$393.00

Fluke Electrical Testers



Fluke T6-1000 Electrical Tester

Measure voltage the same way you measure current.

BE SAFER

Measure voltage to 1000V AC through the open jaw, without the need for test leads.

BE FASTER

No need to open covers or remove wire nuts.

BE MORE EFFICIENT

Simultaneously measure voltage and current.

Fluke T6-600 Deal



Purchase
Fluke T6-600
Electrical Tester



Receive FREE
Fluke H-T6
Holster

Valued at \$72.00

Fluke T6-1000 Deal



Purchase
Fluke T6-1000
Electrical Tester



Receive FREE
Fluke C150 Soft
Case + AC285
Alligator Clips

Valued at \$148.00

Fluke Front Line Infrared Cameras

Fluke PTi120 Pocket Infrared Camera and TiS20+ Infrared Camera



- Get the context of the visual and infrared details all in one precisely blended or picture-in-picture image with IR-Fusion® technology
- Automatically organise and file infrared images with the Fluke Connect® App
- -20 °C to +150 °C temperature measurement range

Fluke PTi120 Deal



Purchase
Fluke PTi120 Pocket
Infrared Camera



Receive FREE
Fluke 417D
Laser Distance Meter

Valued at \$183.00

Fluke TiS20+ Deal



Purchase
Fluke TiS20+
Infrared Camera



Receive FREE
Fluke 417D +
C1600 Hard Case

Valued at \$311.00

Fluke Laser Distance Meter

NEW

- Instantly measure up to 40 metres with 1-button point-and-click
- Continuous measurement capable: adjusting as you move closer and farther from your target
- 1 metre drop tested and IP54 rated

Fluke 417D Deal



Purchase
Fluke 417D Laser
Distance Meter
or
Fluke 417D/
62 MAX+
IR Thermometer Kit



Receive FREE
Fluke 1AC
VoltAlert™
Electrical Tester

Valued at \$83.00





BUNDLE & SAVE

FLUKE®



Fluke 179 IMSK Industrial Multimeter Service Kit

Includes:

- Fluke 179 True-RMS Digital Multimeter
- Fluke 323 True-RMS Clamp Meter
- 80BK-A DMM Temperature Probe
- TL75 Hard Point Test Lead Set
- AC175 Threaded Alligator Clip Set



Fluke 87V IMSK Industrial Multimeter Service Combo Kit

Includes:

- Fluke 87V Industrial Multimeter
- i400 400 A AC Current Clamp
- 80BK-A DMM Temperature Probe
- TL75 Hard Point Test Lead Set
- AC175 Threaded Alligator Clip Set



Fluke 289 IMSK Industrial Multimeter Service Kit

Includes:

- Fluke 289 True-RMS Data Logging Multimeter
- i400 400A AC Current Clamp
- TL71 Flexible Silicone Test Lead Set
- AC175 Threaded Alligator Clip Set

Fluke 179 IMSK Kit Deal



Receive FREE
Fluke 7pc
Insulated
Screwdriver Set

Valued at \$110.00

Fluke 87V/289 IMSK Kit Deal



Receive FREE
Fluke Pack30 Professional
Tool Backpack

Valued at \$335.00

Fluke High Resolution Diagnostic Scopes



Fluke DS701 and DS703 FC Diagnostic Scope

- High definition probe with dual-view camera
- High Resolution:
 - DS701 - 800 x 600 (480,000 pixels)
 - DS703 FC- 1200 x 720 (864,000 pixels)
- Processing speeds that render a smooth, clear, consistent image
- 7" LCD screen for easy viewing

Fluke Diagnostic Scope Deal



Purchase
Fluke DS701 or
DS703 FC
Diagnostic Scope



Receive FREE
Fluke 150 Lumen
Intrinsically Safe
Flashlight

Valued at \$160.00

How to redeem your FREE gift:

1. Purchase a selected Fluke test tool in this promotion between 07th May 2020 and 30th June 2020
2. Redeem online at www.fluke.co/EOFY before COB 14th July 2020

Sponsored by Fluke Australia Pty Ltd. Free tool prices are Fluke Australia's recommended trade price. Final pricing is at the discretion of the participating authorised Fluke Australia distributor or wholesaler. Consumers purchasing via a wholesaler branch need to ensure the select branch is purchasing Fluke equipment from a Fluke Australia authorised distributor which can be found here: www.fluke.com/au/wtb to be valid to redeem within this promotion. All redemptions will be checked and verified by Fluke Australia. Fluke rewards can be redeemed online only at: www.fluke.co/EOFY with proof of purchase. Offer is valid for purchases made between 07 May 2020 till 30 June 2020 or until stocks last. Offers cannot be combined with any other discounts, promotions or other special offers. Allow 6-8 weeks delivery of reward items. Deals only available to Australian residents.