

**NEW SEASON  
NEW TOOLS**

**FLUKE SALE**



Offers valid until 2nd Oct 2020 or until stocks last

**Fluke 370 Series True-RMS Clamp Meters**

The Fluke 370 Series of True-RMS Clamp Meters provides a range of state-of-the-art features to meet even the most demanding job requirements.

All 3 of the clamp meters have improved base features such as a large, backlit display, True-RMS standard, CAT IV safety rating and a durably constructed body. Additionally, the 376 FC, 375 FC and 374 FC are a part of the Fluke Connect® family of wireless test tools and are compatible with the iFlex™ Flexible Current Probe (included with the 376 FC, sold separately for the 375 FC and 374 FC), and provide increased measurement readings to 1000 A and 1000 V AC and DC.

Function/Features	374 FC	375 FC	376 FC
Jaw Opening	34 mm	34 mm	34 mm
Current True RMS AC/DC	600 A AC/DC	600 A AC/DC	1000 A AC/DC
Voltage AC/DC	1000 V	1000 V	1000 V
Continuity/Resistance	•/•	•/•	•/•
Capacitance	•	•	•
Frequency	-	•	•

**Fluke 374 & 375 FC Series Deal**



**Purchase**  
Fluke 374 or 375 FC  
True-RMS Clamp Meters

**Receive FREE**  
Fluke 7pc Insulated  
Screwdriver Set  
**Valued at \$115.00**

**Fluke 376 FC Deal**



**Purchase**  
Fluke 376 FC  
True-RMS Clamp Meter

**Receive FREE**  
Fluke Insulated Hand  
Tools Starter Kit  
**Valued at \$318.00**

# Fluke Digital Multimeters



## When Uptime Matters

Whether you work in the residential or commercial world, deal with HVAC equipment or electricity Fluke has a full family of digital multimeters for you.

## Fluke 110 Series Digital Multimeter

Features	114	115	116	117
True RMS Readings	AC	AC	AC	AC
Voltage AC/DC	600 V	600 V	600 V	600 V
Current AC/DC	-	10.0 A	600.0 $\mu$ A	10.0 A
Temperature	-	-	+400°C	-
Diode Test	-	Yes	Yes	Yes
LoZ	Yes	-	Yes	Yes
Safety Rating (EN 61010)	CAT III 600V	CAT III 600V	CAT III 600V	CAT III 600V

### Fluke 110 Series Deal



**Purchase**  
Fluke 114,  
115, 116 or  
117 Digital  
Multimeter



**Receive FREE**  
Fluke TPAK ToolPak™  
Magnetic Meter Hanger  
+ Fluke Ergonomic  
Bottle Opener

**Valued at \$108.00**



## Fluke 179 True-RMS Digital Multimeter

- True RMS voltage and current measurements
- 0.09% basic accuracy
- 6000 count resolution
- Temperature measurements

### Fluke 179 Deal



**Purchase**  
Fluke 179  
True-RMS  
Digital  
Multimeter



**Receive FREE**  
Fluke TLK225 Master  
Accessory Set

**Valued at \$282.00**

**NEW**



## Fluke 87V MAX True-RMS Digital Multimeter

- Waterproof, dustproof IP67 case withstands drops up to 4-metres
- Supports accurate measurements on VFDs using a low-pass filter
- Captures intermittents as fast as 250  $\mu$ S with Peak Capture

### Fluke 87V MAX Deal



**Purchase**  
Fluke 87V MAX  
Industrial  
Multimeter



**Receive FREE**  
Fluke TLK289 Industrial  
Master Test Lead Set

**Valued at \$314.00**



## Fluke 1587 FC Insulation Multimeter

- PI/DAR timed ratio tests
- Live circuit detection prevents insulation test if voltage > 30 V is detected for added user protection
- VFD low-pass filter for accurate motor drive measurements

### Fluke 1587FC Deal



**Purchase**  
Fluke 1587 FC  
Insulation  
Multimeters



**Receive FREE**  
Fluke 325 True  
RMS Clamp Meter

**Valued at \$393.00**

# Fluke Electrical Testers



## Fluke T6-1000 Electrical Tester

Measure voltage the same way you measure current.

### BE SAFER

Measure voltage to 1000V AC through the open jaw, without the need for test leads.

### BE FASTER

No need to open covers or remove wire nuts.

### BE MORE EFFICIENT

Simultaneously measure voltage and current.

### Fluke T6-600 Deal



**Purchase**  
Fluke T6-600  
Electrical Tester



**Receive FREE**  
Fluke H-T6  
Holster

**Valued at \$72.00**

### Fluke T6-1000 Deal



**Purchase**  
Fluke T6-1000  
Electrical Tester



**Receive FREE**  
Fluke C150 Soft  
Case + AC285  
Alligator Clips

**Valued at \$148.00**

# Fluke Front Line Infrared Cameras

## Fluke PTi120 Pocket Infrared Camera and TiS20+ Infrared Camera



- Get the context of the visual and infrared details all in one precisely blended or picture-in-picture image with IR-Fusion® technology
- Automatically organise and file infrared images with the Fluke Connect® App
- -20 °C to +150 °C temperature measurement range



### Fluke PTi120 Deal



**Purchase**  
Fluke PTi120 Pocket  
Infrared Camera



**Receive FREE**  
Fluke 417D  
Laser Distance Meter

**Valued at \$183.00**

### Fluke TiS20+ Deal



**Purchase**  
Fluke TiS20+  
Infrared Camera



**Receive FREE**  
Fluke 417D +  
C1600 Hard Case

**Valued at \$311.00**

# Fluke Laser Distance Meter

**NEW**

- Instantly measure up to 40 metres with 1-button point-and-click
- Continuous measurement capable: adjusting as you move closer and farther from your target
- 1 metre drop tested and IP54 rated

### Fluke 417D Deal



**Purchase**  
Fluke 417D Laser  
Distance Meter  
or  
Fluke 417D/  
62 MAX+  
IR Thermometer Kit



**Receive FREE**  
Fluke 1AC  
VoltAlert™  
Electrical Tester

**Valued at \$83.00**





**Fluke 179 IMSK Industrial Multimeter Service Kit**

**Includes:**

- Fluke 179 True-RMS Digital Multimeter
- Fluke 323 True-RMS Clamp Meter
- 80BK-A DMM Temperature Probe
- TL75 Hard Point Test Lead Set
- AC175 Threaded Alligator Clip Set



**Fluke 87V IMSK Industrial Multimeter Service Combo Kit**

**Includes:**

- Fluke 87V Industrial Multimeter
- i400 400 A AC Current Clamp
- 80BK-A DMM Temperature Probe
- TL75 Hard Point Test Lead Set
- AC175 Threaded Alligator Clip Set



**Fluke 289 IMSK Industrial Multimeter Service Kit**

**Includes:**

- Fluke 289 True-RMS Data Logging Multimeter
- i400 400A AC Current Clamp
- TL71 Flexible Silicone Test Lead Set
- AC175 Threaded Alligator Clip Set

**Fluke 179 IMSK Kit Deal**



**Receive FREE**  
Fluke 7pc  
Insulated  
Screwdriver Set

**Valued at \$115.00**

**Fluke 87V/289 IMSK Kit Deal**



**Receive FREE**  
Fluke Pack30 Professional  
Tool Backpack

**Valued at \$335.00**

**Fluke High Resolution Diagnostic Scopes**



**Fluke DS701 and DS703 FC Diagnostic Scope**

- High definition probe with dual-view camera
- High Resolution:
  - DS701 - 800 x 600 (480,000 pixels)
  - DS703 FC- 1200 x 720 (864,000 pixels)
- Processing speeds that render a smooth, clear, consistent image
- 7" LCD screen for easy viewing

**Fluke Diagnostic Scope Deal**



**Purchase**  
Fluke DS701 or  
DS703 FC  
Diagnostic Scope



**Receive FREE**  
Fluke 150 Lumen  
Intrinsic Safe  
Flashlight

**Valued at \$160.00**

**How to redeem your FREE gift:**

1. Purchase a selected Fluke test tool in this promotion between 7th Sep 2020 and 2nd Oct 2020
2. Redeem online at [www.fluke.co/SPRING](http://www.fluke.co/SPRING) before COB 16th Oct 2020

Sponsored by Fluke Australia Pty Ltd. Free tool prices are Fluke Australia's recommended trade price. Final pricing is at the discretion of the participating authorised Fluke Australia distributor or wholesaler. Consumers purchasing via a wholesaler branch need to ensure the select branch is purchasing Fluke equipment from a Fluke Australia authorised distributor which can be found here: [www.fluke.com/au/wtb](http://www.fluke.com/au/wtb) to be valid to redeem within this promotion. All redemptions will be checked and verified by Fluke Australia. Fluke rewards can be redeemed online only at: [www.fluke.co/SPRING](http://www.fluke.co/SPRING) with proof of purchase. Offer is valid for purchases made between 07 Sep 2020 till 2nd Oct 2020 or until stocks last. Offers cannot be combined with any other discounts, promotions or other special offers. Allow 6-8 weeks delivery of reward items. Offers valid to Australian and New Zealand residents.