

SAVE
20%

LIMITED TIME OFFER

FLUKE
ACOUSTIC
IMAGERS

SEE SOUND & PARTIAL DISCHARGE



Try the virtual demo
fluke.co/ii9xx20vd

Specification	ii900
Detection	Compressed air, gas, and vacuum leaks
Sound Pressure Sensitivity	Detects a 2.5 cm ³ /sec leak at 7 bar from up to 10 metres
Frequency Band	2 kHz to 52 kHz
# of microphones	64 digital MEMS microphones
Operation Distance Range	0.5 to > 70 metres
Battery Life	6 hours

Specification	ii910
Detection	Compressed air, gas, and vacuum leaks, HV corona discharge, partial discharge, surface tracking, and arcing
Frequency Band	2 kHz to 100 kHz
# of microphones	64 digital MEMS microphones
Operation Distance Range	0.5 to 120 metres
Battery Life	6 hours

FLUKE II900 AND FLUKE II910 LIMITED TIME OFFER



RECEIVE 20% OFF
Scan for more info: fluke.co/ii9xx20

Fluke ii900 and ii910 Acoustic Imager purchases only

Valid for purchases between **4th March to 30th June 2024**.
Speak to your Fluke reseller for more information.