

GEAR UP FOR TAX TIME

FLUKE®



Offers end 30th June 2019

NEW

Fluke PTi120 Pocket Thermal Camera

Get the infrared troubleshooting power you need that fits right in your pocket.

- Fully radiometric thermal imager gives you measurement data to the pixel with 120 x 90 infrared resolution (10,800 pixels)
- 3.5" LCD touchscreen display for easy troubleshooting
- -20 °C to +150 °C temperature measurement range
- Automatically organise and file thermal images with Fluke Connect®
- Six colour palettes
- Withstands 1 metre drop
- IP 54 enclosure rating



Join the Conversation
@FlukeAustralia



Fluke Insulated Hand Tools Available June 2019

NEW

1000 Volt Insulated Hand Tools. Lifetime Warranty.

Forged from German steel, Fluke now offers a line of 11 premium insulated hand tools that are built to last a lifetime. That's why they carry a lifetime warranty.* Fluke insulated tools always feel right. From the moment you first put them in your hand, you're ready to go to work. The pliers offer a smooth, solid motion, without a need for break-in. The screwdrivers give you maximum torque and a comfortable grip that reduces fatigue.

Fluke Insulated Pliers and Cutters



Heavy duty, high leverage diagonal cutter

- Cuts hard materials including steel and piano wire
- Power joint and precision cutting edges



Long nose pliers with side cutter and gripping zones

- Unique milled wave pattern gripping zones
- 4 gripping points for pulling round objects with superior grip
- Straight, half-round, long and slim knurled jaws



Heavy duty combination pliers

- Secure hold by aggressive serrated jaws and 4-point gripping hole
- Slim shape to reach wires in tight spaces
- Powerful gripping jaw, yet 20 % lighter weight than other designs



Fast adjust pump pliers

- 27 jaw adjustment steps for more accurate gripping
- Improved access to the workpiece in tight spaces due to slim size
- Self-locking on pipes and nuts: no slipping on the workpiece with low hand force required

Fluke Screwdrivers



Slot-head drivers

Fluke model	Description
ISLS3	Insulated Slotted Screwdriver 2.5 mm x 75 mm, 1,000 V
ISLS5	Insulated Slotted Screwdriver 4 mm x 100 mm, 1,000 V
ISLS8	Insulated Slotted Screwdriver 6 mm x 125 mm, 1,000 V



Phillips-head drivers

Fluke model	Description
IPHS1	Insulated Phillips Screwdriver #1, 75 mm, 1,000 V
IPHS2	Insulated Phillips Screwdriver #2, 100 mm, 1,000 V



Square-head drivers

Fluke model	Description
ISQS1	Insulated Squared Screwdriver #1, 100 mm, 1,000 V
ISQS2	Insulated Squared Screwdriver #2, 125 mm, 1,000 V

* Industrial products limited Lifetime Warranty

Each Fluke insulated hand tool will be free from defects in material and workmanship for its lifetime. Lifetime is defined as seven years after Fluke discontinues manufacturing the product, but the warranty period shall be at least fifteen years from date of purchase. The warranty does not cover damage from neglect, misuse, contamination, alteration, accident or abnormal conditions of operation or handling, including damage caused by use outside of the product's intended use. This warranty covers the original purchaser only and is not transferable. To establish original ownership proof of purchase is required.

Fluke Insulated Bundles

**BUNDLE AND
SAVE**



Fluke T6 Electrical Tester + Insulated Hand Tools Starter Kit - IBT6K

- Fluke T6 Electrical Tester
- 3 slotted tips
- 2 Phillips tips
- Long nose pliers
- Heavy duty diagonal cutter
- Heavy duty combination pliers
- Roll-up tool pouch



Fluke 87V Industrial Multimeter + Insulated Hand Tools Starter Kit - IB875K

- Fluke 87V Industrial Multimeter
- 3 slotted tips
- 2 Phillips tips
- Long nose pliers
- Heavy duty diagonal cutter
- Heavy duty combination pliers
- Roll-up tool pouch



Fluke 117 Electrician's Multimeter + Insulated Hand Tools Starter Kit - IB117K

- Fluke 117 Electrician's Multimeter
- 3 slotted tips
- 2 Phillips tips
- Long nose pliers
- Heavy duty combination pliers
- Heavy duty diagonal cutter
- Roll-up tool pouch



Fluke Insulated Tool Kits



Insulated 7 Piece Screwdriver Kit - IKSC7

- 3 slotted tips
- 2 Phillips tips
- 2 square drive tips



Insulated 3 Piece Pliers Kit - IKPL3

- Long nose pliers
- Heavy duty diagonal cutter
- Heavy duty combination pliers
- Roll-up tool pouch



Insulated Hand Tools Starter Kit - IKST7


- 3 slotted tips
- 2 Phillips tips
- Long nose pliers
- Heavy duty diagonal cutter
- Heavy duty combination pliers
- Roll-up tool pouch



Fluke Pack30 Backpack + Insulated Hand Tools Starter Kit - IKPK7

- Fluke Pack30 Professional Tool Backpack
- 3 slotted tips
- 2 Phillips tips
- Long nose pliers
- Heavy duty diagonal cutter
- Heavy duty combination pliers
- Roll-up tool pouch

Fluke Education Program



**Up to 25%
discount
on select
Fluke Tools**

Are you currently an actively enrolled student at a technical and vocation school, college or university?

If so, you could be eligible to Fluke's Student Discount and take advantage of **up to 25% off the list price on select Fluke tools***. Contact one of our Fluke Authorised Educational Distributors to receive your entitled discount at **fluke.com.au/education**

*Terms and conditions apply, to qualify please refer to qualifying details on the Fluke website.

Fluke Multifunction Installation Testers

The Fluke 1662, 1663 and 1664 FC Multifunction Installation Testers are the only installation testers that help prevent damage to connected appliances, while allowing users to wirelessly e-mail results from the field*. The Fluke 1660 Series Testers verify the safety of electrical installations in domestic, commercial and industrial applications. They can ensure that fixed wiring is safe and correctly installed to meet the requirements of all relevant local standards.

- **Insulation PreTest:** Protect the installation and avoid costly mistakes
- **Auto Test:** Reduce test time up to 40% – Start a sequence of seven critical tests with one press of the TEST button
- **Fluke Connect®:** View test results, share and retrieve stored results on your smartphone via the Fluke Connect® mobile app
- **Three-year warranty**

*Fluke 1664 FC/FVF/AU model only



Specifications	1662 AU	1663/FVF AU	1664 FC/FVF AU
Insulation PreTest™ safety functions			•
Insulation at L-N, L-PE, N-PE inputs			•
Auto Test Sequence			•
Fluke Connect® compatibility			•
Test smooth DC sensitive RCD's (Type B/B+)		•	•
Earth resistance		•	•
Covering all basic installation test functions	•	•	•
Fluke FVF-SC2 reporting software included		•	•

Fluke 1662 Gear Up Deal



Buy

Fluke 1662/AU Multifunction Installation Tester

A solid, basic installation tester that gives you Fluke reliability, simple operation and all the testing power you need for day-in, day-out installation testing.



Receive FREE
Fluke T5-1000
Voltage, Continuity
& Current Tester

Valued at \$309.00

Fluke 1663 Gear Up Deal



Buy

Fluke 1663/FVF/AU Multifunction Installation Tester with FlukeView® Documenting Software

Ideal tester for professional troubleshooters with high-end functionality and advanced measurement capability.



Receive FREE
Fluke T6-600
Electrical Tester

Valued at \$352.00

Fluke 1664 FC Gear Up Deal



Buy

Fluke 1664 FC/FVF/AU Multifunction Installation Tester with Fluke Connect™ and FlukeView® Documenting Software

Protect appliances, share results wirelessly with Fluke Connect, perform 7 tests with 1 touch.



Receive FREE
Fluke T6-1000
Electrical Tester

Valued at \$424.00

Sponsored by Fluke Australia Pty Ltd. Free tool prices are Fluke Australia's recommended trade price. Final pricing is at the discretion of the participating authorised Fluke Australia distributor or wholesaler. Consumers purchasing via a wholesaler branch need to ensure the select branch is purchasing Fluke equipment from a Fluke Australia authorised distributor which can be found here: www.fluke.com/au/wtb to be valid to redeem within this promotion. All redemptions will be checked and verified by Fluke Australia. Fluke rewards can be redeemed online only at: www.fluke.com.au/gearup with proof of purchase. Offer is valid for purchases made between 20 May 2019 till 30 June 2019 or until stocks last. Offers cannot be combined with any other discounts, promotions or other special offers. Allow 6-8 weeks delivery of reward items.

Fluke Digital Multimeters

Fluke 110 Series Digital Multimeters

Five models within the Fluke series (117, 116, 115, 114 and 113). Dependable True-RMS Digital Multimeters with a large 3-1/2 digit / 6000 count display for electrical and HVAC use.

Fluke Multimeter Gear Up Deal

Buy
Fluke 113, 114,
115, 116 or 117
Digital Multimeter

Receive FREE
Fluke C23
Carrying Case



Valued at \$59.00

Function/features	113	114	115	116	117
True RMS Readings	AC	AC	AC	AC	AC
Voltage AC/DC	600 V	600 V	600 V	600 V	600 V
Current AC/DC	-	-	10.0 A	600.0 μ A	10.0 A
Temperature	-	-	-	+400 $^{\circ}$ C	-
Diode Test	Yes	-	Yes	Yes	Yes
Safety Rating (EN 61010)	CAT III 600V	CAT III 600V	CAT III 600V	CAT III 600V	CAT III 600V

Fluke 80-5 Digital Multimeter Series

From the control room to the plant floor, the Fluke 80 Series family of digital multimeters has earned its reputation as the digital multimeter industrial technicians trust.

PRICE DROP

UP TO 25% OFF
FROM \$710
Excluding GST

Fluke 80-5 Digital Multimeter Series

- Accurate voltage and frequency measurements on adjustable speed motor drives and other equipment
- Built-in thermometer allows for temperature readings without having to carry a separate instrument



Function/features	Fluke 83V	Fluke 87V	Fluke 88V
True RMS Readings	-	AC	AC
Voltage AC/DC	1000 V	1000 V	1000 V
Current AC/DC	10.0 A	10.0 A	10.0 A
Temperature	-	+ 1090 $^{\circ}$ C	+ 1090 $^{\circ}$ C
Diode Test	Yes	Yes	Yes
Motor Drive Measurements	No	Yes	No
RPM	No	No	Yes
Safety Rating (EN 61010)	CAT IV 600V CAT III 1000V	CAT IV 600V CAT III 1000V	CAT IV 600V CAT III 1000V

Fluke Clamp Meters



Fluke 37X Series Clamp Meters

The Fluke 370 Series of True-RMS Clamp Meters provides a range of state-of-the-art features to meet even the most demanding job requirements.

Function/features	373	374 FC	375 FC	376 FC
Jaw Opening (mm)	32	34	34	34
Current True RMS AC/DC	600 A AC	600 A AC/DC	600 A AC/DC	1000 A AC/DC
Voltage AC/DC	600 V	1000 V	1000 V	1000 V
Continuity/Resistance	•/•	•/•	•/•	•/•
Capacitance / Frequency / Temperature	-/-/-	•/-/-	•/•/-	•/•/-

Fluke Clamp Gear Up Deal

Buy
Fluke 376 FC
Clamp Meter

Receive FREE
Fluke 114 Digital
Multimeter



Valued at \$267.00



Point, Line and Rotary Lasers

Get the job done faster with the next generation of PLS laser levels

As a Fluke Company, PLS has incorporated Fluke's high standards for accuracy, ruggedness, and dependability so you can trust your laser will maintain its precision for years to come. From point, line to rotary, PLS laser levels provide bright, crisp reference points and lines for quick and accurate layout of many interior or exterior jobs.

The range includes: PLS3, PLS5, PLS6, PLS180 Line Laser Levels and PLSH2 Rotary Laser Levels.

All versions are available in red and green.

- Beam quality is bright, thin and crisp
- Drop tested with water and dust Ingress Protection (IP)
- Designed for the professional contractor with self leveling technology
- 3-year warranty

PLS Laser Level Gear Up Deal

Buy
PLS 6R/G or 180R/G
Laser Level or Kit



Receive FREE
PLS SLD Line Laser
Detector



Valued up to \$292.00



	Point and Line Lasers: PLS 3, 5, 6, 180	Rotary Lasers: PLS H2, HV2R, HV2G
Accuracy	3mm at 10 metres	≤2.2 mm at 30 metres
Working Range	61 metres w/ SLD Detector	300 metres radius w/ XLD Detector
Power Supply	3 x AA Alkaline IEC Batteries	4 x D Alkaline or NiMH Rechargeable
Fan Angle: (PLS 180R, 180G, 6R, 6G)	180° horizontal; 130° vertical	
Self-leveling Range	4°	4.5°
Operating Temperature	-10 °C to +50 °C	-10 °C to +50 °C
Ingress Protection	IP54	IP67

How to redeem your FREE gift with your purchase:

1. Purchase a selected Fluke test tool in this promotion between 20th May 2019 and 30th June 2019.
2. Redeem online at www.fluke.com.au/gearup before COB 14th July 2019

Sponsored by Fluke Australia Pty Ltd. Free tool prices are Fluke Australia's recommended trade price. Final pricing is at the discretion of the participating authorised Fluke Australia distributor or wholesaler. Consumers purchasing via a wholesaler branch need to ensure the select branch is purchasing Fluke equipment from a Fluke Australia authorised distributor which can be found here: www.fluke.com.au/wtb to be valid to redeem within this promotion. All redemptions will be checked and verified by Fluke Australia. Fluke rewards can be redeemed online only at: www.fluke.com.au/gearup with proof of purchase. Offer is valid for purchases made between 20 May 2019 till 30 June 2019 or until stocks last. Offers cannot be combined with any other discounts, promotions or other special offers. Allow 6-8 weeks delivery of reward items. Deals only available to Australian residents.