



FLUKE®

UNDER PRESSURE?

Buy the Fluke 729 Automatic Pressure Calibrator or Fluke 754 Process Calibrator and get a **FREE** Fluke Pressure Module or Gauge worth up to \$2,000.

Between August 12 and December 20, 2019, purchase a Fluke 729 or Fluke 754 Calibrator and receive your choice of a select Fluke pressure tool.

The Fluke 729:


- Automatic pressure generation and regulation to 0 to 20 Bar
- Automatic internal fine-pressure adjustment
- Built-in leak testing for verifying test setups for leakage
- Save time and effort when testing and calibrating HART® enabled pressure transmitters

The Fluke 754:

- Calibrate temperature, pressure, voltage current, resistance and frequency
- Easily troubleshoot HART® instrumentation
- Document field calibration results
- Newer software, improved battery life, USB port and 99.7 % confidence level

Save up to \$4,000 when you bundle up with software

Fluke process calibrators
Work smarter. Work faster.



Here's how to redeem:

1. Purchase a Fluke 729 Automatic Pressure Calibrator or Fluke 754 Documenting Process Calibrator from a Fluke Australia Authorised Distributor between August 12, 2019 and December 20, 2019.
2. Redeem online at www.fluke.co/underpressure before COB January 03 2019.

Pressure modules

Choose one (1) tool from the list below as your free gift with each Fluke 729 Automatic Pressure Calibrator or Fluke 754 Documenting Process Calibrator purchased. Select the model number of your chosen module or gauge on the online redemption form.

750P00	0 to 1 Inch H2O (0 to 2.5 mBar)
750P01	0 to 10 Inch H2O (0 to 25 mBar)
750P02	0 to 1 PSI (0 to 70 mBar)
750P22	0 to 1 PSI (0 to 70 mBar)
750P03	0 to 5 PSI (0 to 350 mBar)
750P23	0 to 5 PSI (0 to 350 mBar)
750P04	0 to 15 PSI (0 to 1 Bar)
750P24	0 to 15 PSI (0 to 1 Bar)
750P05	0 to 30 PSI (0 to 2 Bar)
750P06	0 to 100 PSI (0 to 7 Bar)
750P27	0 to 300 PSI (0 to 20 Bar)
750P07	0 to 500 PSI (0 to 35 Bar)
750P08	0 to 1000 PSI (0 to 70 Bar)
750P09	0 to 1500 PSI (0 to 100 Bar)
750P2000	0 to 2000 PSI (0 to 140 Bar)
750P29	0 to 3000 PSI (0 to 200 Bar)
750P30	0 to 5000 PSI (0 to 340 Bar)
750P31	0 to 10000 PSI (0 to 700 Bar)
750PA3	0 to 5 PSI (0 to 350 mBar)
750PA4	0 to 15 PSI (0 to 1 Bar)
750PA5	0 to 30 PSI (0 to 2 Bar)
750PA6	0 to 100 PSI (0 to 7 Bar)
750PA27	0 to 300 PSI (0 to 20 Bar)
750PA7	0 to 500 PSI (0 to 35 Bar)
750PA8	0 to 1000 PSI (0 to 70 Bar)

750PA9	0 to 1500 PSI (0 to 100 Bar)
750PV3	-5 PSI (-350 mBar)
750PV4	-15 PSI (-1 Bar)
750PD2	-1 to 1 PSI (-70 to 70 mBar)
750PD3	-5 to 5 PSI (-350 to 350 mBar)
750PD10	-10 to 10 PSI (-700 to 700 mBar)
750PD4	-15 to 15 PSI (-1 to 1 Bar)
750PD5	-15 to 30 PSI (-1 to 2 Bar)
750PD50	-15 to 50 PSI (-1 to 3.5 Bar)
750PD6	-15 to 100 PSI (-1 to 7 Bar)
750PD7	-15 to 200 PSI (-1 to 14 Bar)
750PD27	-15 to 300 PSI (-1 to 20 Bar)
750R04	0 to 15 PSI (0 to 1 Bar)
750R06	0 to 100 PSI (0 to 7 Bar)
750R27	0 to 300 PSI (0 to 20 Bar)
750R07	0 to 500 PSI (0 to 35 Bar)
750R08	0 to 1000 PSI (0 to 70 Bar)
750R29	0 to 3000 PSI (0 to 200 Bar)
750R30	0 to 5000 PSI (0 to 340 Bar)
750R31	0 to 10000 PSI (0 to 700 Bar)
750RD5	-15 to 30 PSI (-1 to 2 Bar)
750RD6	-12 to 100 PSI (-1 to 7 Bar)
750RD27	-12 to 300 PSI (-0.8 to 20 Bar)
750P3IN	0 to 3 inch (0 to 7.5 mBar)
750P5IN	0 to 5 inch (0 to 12.5 mBar)

Pressure gauges

Precision Pressure Gauges:	
700G01	0.4 PSIG/3 kPa
700G02	1 PSIG/7 kPa
700G04	15 PSIG/103 kPa
700G05	30 PSIG/207 kPa
700G06	100 PSIG/300 kPa
700G27	300 PSIG/2070 kPa
700G07	500 PSIG/3400 kPa
700G08	1000 PSIG/6900 kPa
700G10	2000 PSIG/13.6 MPa
700G29	3000 PSIG/20.7 MPa
700G30	5000 PSIG/34 MPa
700G31	10000 PSIG/69 MPa

Absolute Pressure Gauges:	
700GA4	15 PSIA
700GA5	30 PSIA
700GA6	100 PSIA
700GA27	300 PSIA

Offer terms and conditions: Sponsored by Fluke Australia Pty Ltd. Gift with purchase is available for a "Qualifying Fluke Purchase" (Fluke 729 or Fluke 754) made from an authorised Fluke Australia distributor in Australia, New Zealand or the Pacific Island regions between August 12, 2019 and December 20, 2019 at RS Components Pty Ltd. This promotion is applicable to all Fluke 729 and 754 models (incl. software bundles). Customers purchasing via a wholesaler branch need to ensure the select branch is acquiring Fluke equipment from a Fluke Australia authorised distributor which can be found here: www.fluke.com/au/wb to be valid to redeem within the promotion. Final pricing is at the discretion of the participating authorised Fluke Australia distributor or wholesaler. All redemptions will be checked and verified by Fluke Australia. Offers cannot be combined with any other discounts, promotions or other special offers. Allow 6-8 weeks delivery of reward items.